

137102XX_137103XX

Diagram illustrating the connection of the power supply to the device. The power supply is connected to the device terminals. The black cable (marked with a minus sign -) is connected to the BACK terminal. The red cable (marked with a plus sign +) is connected to the FRONT terminal.

Drive Current (mA)	Forward Voltage		Power (W)
	min (Vf)	max (Vf)	
350	11,2	13,2	4,1
500	11,2	13,2	6,1

For serial connection, respect polarity!
Not suited for connection to mains voltage.
Combine with a Modular LED-driver.

Replace protective shield when broken. The luminaire shall only be used complete with its protective shield.
Reference number: 1014378




Touching the LED can result in permanent damage of the light source. The light source and/or driver contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.



A discharge of static electricity may damage sensitive components. Therefore do not touch the LED nor the stripped parts of the wires with bare hands. Always be properly insulated by using ESD gloves.

For latest version of driver matrix and available accessories check www.supermodular.com or connect with your sales contact.

Recessed ring Ø50
13642030



Concrete ring Ø50 for standard concrete boxes
13642130

