


Médard 70 stretched semi-recessed 2x LED


116530XX_116531XX_116532XX_116533XX




Drive Current (mA)	Forward Voltage		Power (W)
	min (Vf)	max (Vf)	
350	29,1	33,7	11,0
500	29,9	34,7	16,2

For serial connection, respect polarity!

⊕ RED ⊖ BLACK






10mm
□ 0,08 - 2,5mm²

screws not included

≤ Ø4 mm
≤ Ø8 mm



	LIGHT SOURCE - DO NOT TOUCH LED Touching the LED can result in permanent damage of the light source. The light source contained in this luminaire shall only be replaced by the manufacturer or his service agent or a similar qualified person.
	PREVENTING ELECTROSTATIC DAMAGE A discharge of static electricity may damage sensitive components. Always be properly grounded when touching leads or circuitry inside the luminaire. Use a wrist strap connected by a ground cord to the housing. Avoid touching the light sources with bare hands.
DRIVERS & ACCESSORIES For latest version of driver matrix and available accessories check www.supermodular.com or connect with your sales contact.	



V1 - 03/01/2019

